

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010179

Status:

Active

Overview:

Description:

GWconnect Turned Crimp Contact for 16A Inserts and Modules, Female, Silver (Ag)
Plated Copper Alloy, 2.50mm² (14 AWG), 100 per Bag

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp
Overview	hdc_heavy_duty_connectors
Product Category	Contacts
Product Name	GWconnect
UPC	887191874975
Physical	
Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	1.450/g
Number of Grooves	3
Packaging Type	Bag
Stripping Length	7.50mm
Wire Size AWG	14
Wire Size mm²	2.50
Electrical	
Current - Maximum per Contact	16.0A
Material Info	
Engineering Number	7300.6244.0

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with

Exemption 6(c)

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93601 Series

Mates With

93601 Male Turned Crimp Contact

Use With

S-AC, S-EC, S-EE, S-EEE, S-EHV,S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0179