

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010229

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Spring Terminal Insert, Male, 10-Pole, 16A, Silver (Ag) Plated Contacts, Size 10B «57x27»

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Component Size		10B «57X27»
Component Type		Inserts - Spring Terminal
Insert Series		S-ES
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC		887191877877
Physical		
Durability (mating cycles max)		500
Flammability		UL 94V-0
Gender		Male
Insert Color		Grey
Material - Contact		Copper Alloy
Material - Insert		Polycarbonate
Material - Plating		Silver
Net Weight		61.930/g
Number of Rows		2
Packaging Type		Bag
Polarized to Mating Part		Yes
Poles		10
Stripping Length		9.00-11.00mm
Temperature Range - Operating		-40° to +125°C
Wire Size AWG		14-26
Wire Size mm²		0.14-2.50
Electrical		
Current - Maximum per Contact		16.0A
Voltage - Maximum		500V
Material Info		
Engineering Number		7310.5952.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93601 Series

Mates With

936010227 Female Spring Terminal Insert

Use With

Size 10B «57x27» Hoods and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0229