

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010230](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Push-in Terminal Insert, Male, 10-Pole, 16A, Silver (Ag) Plated Contacts, Size 10B «57x27»

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Stranded wire with bush terminal 0.14-2.50 (26-14 AWG), Stranded wires with single strand greater than and equal to 0.20mm (16-12 AWG), and Solid wires 0.50-2.50 (20-14 AWG)
Component Size	10B «57X27»
Component Type	Inserts - Push-in Terminal
Insert Series	S-EP
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191877884
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Contact	Copper Alloy
Material - Insert	Polycarbonate
Material - Plating	Silver
Net Weight	70.000/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	10
Stripping Length	9.00-11.00mm
Temperature Range - Operating	-40° to +125°C
Wire Size AWG	12-16, 14-20, 14-26
Wire Size mm²	0.14-2.50, 0.50-2.50, 1.50-4.00
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	500V
Material Info	
Engineering Number	7310.5962.0



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Green Image Not Relevant Not Contained	

Search Parts in this Series
[93601](#) Series

Mates With
[936010228](#) Female Pushin Terminal Insert

Use With
Size 10B «57x27» Hoods and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0230](#)