

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010249](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Crimp Contact Insert, Female, 14-Pole, 10A and 40A, Size 16B «77x27»](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16B «77X27»
Component Type	Inserts - Crimp Contact
Insert Series	S-K12/2
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191879079
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Female
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	80.800/g
Number of Rows	3
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	14
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	10.0A, 40.0A
Voltage - Maximum	250V / 690V
Material Info	
Engineering Number	7314.6040.0



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[93601](#) Series

Mates With
[936010250](#) Male Screw Terminal Block Insert

Use With
Size 16B «77x27» Hoods and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0249