


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010307](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Screw Terminal Insert, Male, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27»



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	24B «104X27»
Component Type	Inserts - Screw Terminal
Insert Series	S-E
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191882550
Physical	
Durability (mating cycles max)	700
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Contact	Copper Alloy
Material - Insert	Polycarbonate
Material - Plating	Silver
Net Weight	111.800/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	24
Stripping Length	7.00mm
Temperature Range - Operating	-40° to +125°C
Tightening Test Torque	0.50 Nm
Wire Size AWG	14-20
Wire Size mm²	0.50-2.50
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	500V
Wire Protection	Yes
Material Info	
Engineering Number	7324.6107.0

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Contained Per - D(2020)9139-DC (19 Jan 2021) Lead Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Green Image Not Relevant Not Contained	

Search Parts in this Series
[93601](#) Series

Mates With
[936010297](#) Female Screw Terminal Insert

Use With
Size 24B «104x27» Hoods and Housings

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0307](#)