

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010332

Status:


Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Crimp Contact Terminal Insert, Male, 64-Pole, Size 24B «104x27»



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	24B «104X27»
Component Type	Inserts - Crimp Contact
Insert Series	S-EEE
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191883809
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Lock to Mating Part	Yes
Material - Insert	Polycarbonate
Net Weight	67.930/g
Number of Rows	8
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	64
Temperature Range - Operating	-40° to +125°C
Wire Size AWG	12-26
Wire Size mm²	0.14-4.00
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	500V
Material Info	
Engineering Number	7364.6197.0

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

- Search Parts in this Series

93601 Series
- Mates With

936010331 Female Crimp Terminal Insert
- Use With

Size 24B «104x27» Hoods and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0332