

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936010408
Status: Active
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Turned Crimp Contact for 40A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 2.50mm² (14 AWG), 100 per Bag



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 936010406-S00 \(PDF\)](#)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
UPC	887191888668
Physical	
Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	2.390/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	9.00mm
Wire Size AWG	14
Wire Size mm ²	2.50
Electrical	
Current - Maximum per Contact	40.0A
Material Info	
Engineering Number	7600.5701.0
Reference - Drawing Numbers	
Product Specification	936010406-S00
Sales Drawing	936010412-000

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Contained Per - ED/71/2019 (16 July 2019) Lead Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
93601 Series

Mates With
93601 Male Turned Crimp Contact

Use With
S-K, S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0408