

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010409

Status:

Active

Overview:

GWconnect® Heavy Duty Connectors (HDC)

Description:

GWconnect Turned Crimp Contact for 40A Inserts and Modules, Female, Gold (Au)
Plated Copper Alloy, 2.50mm² (14 AWG), 100 per Bag



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp Contact
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
UPC	887191888675
Physical	
Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Gold
Net Weight	2.390/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	9.00mm
Wire Size AWG	14
Wire Size mm²	2.50
Electrical	
Current - Maximum per Contact	40.0A
Material Info	
Engineering Number	7600.5701.1

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Not Reviewed

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

93601 Series

Mates With

93601 Male Turned Crimp Contact

Use With

S-K, S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0409