

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010414

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Turned Crimp Contact for 40A Modules, Female, Silver (Ag) Plated Copper Alloy, 10.00mm² (7 AWG), 100 per Bag

Documents:

[Drawing \(PDF\)](#)

[Product Specification 936010406-S00 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA256883

ULE249674

General

Product FamilyIndustrial Connectors / Enclosures

Series93601

Contact TypeTurned Crimp

OverviewGWconnect Heavy Duty Connectors (HDC)

Product CategoryContacts

Product NameGWconnect

UPC887191889221

Physical

GenderFemale

Material - ContactCopper Alloy

Material - PlatingSilver

Net Weight3.000/g

Number of Grooves0

Packaging TypeBag

Stripping Length15.00mm

Wire Size AWG7

Wire Size mm²10.00

Electrical

Current - Maximum per Contact40.0A

Material Info

Engineering Number7600.5704.0

Reference - Drawing Numbers

Product Specification936010406-S00

Sales Drawing936010412-000

Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601](#) Series

Mates With

[93601](#) Male Turned Crimp Contact

Use With

S-M Modules

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0414