

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010433

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Screw Axial Terminal Insert, Male, 2-Pole, 40A, Silver (Ag) Plated Contacts, Size 3A «21x21», with Insulating Shrink Tube, 2.50-6.00mm² wire

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	3A «21x21»
Component Type	Inserts - Screw Axial Terminal
Insert Series	S-Q2/0
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191890418
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Contact	Copper Alloy
Material - Insert	Polycarbonate
Material - Plating	Silver
Net Weight	29.900/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	2
Stripping Length	8.00mm
Temperature Range - Operating	-40° to +125°C
Tightening Test Torque	1.80Nm
Wire Size AWG	10-14
Wire Size mm²	2.50-6.00
Electrical	
Current - Maximum per Contact	40.0A
Voltage - Maximum	830V
Material Info	
Engineering Number	7602.5918.0



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Mates With

936010429 Female Screw Axial Terminal Insert

Use With

Size 3A «21x21» Hoods and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0433](#)