

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010438](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Crimp Contact Insert, Male, 4-Pole-40A and 2-Pole-10A, for Crimp Contacts, Size QD](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	QD
Component Type	Inserts - Crimp Contact
Insert Series	S-QD4/2
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, Desina ISO23570-1, EN 60664-1, EN 61984, UL 1977
UPC	887191890463
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	20.000/g
Number of Rows	3
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	6
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	16.0A, 4px40A+2px10A
Voltage - Maximum	250V / 400V / 690V
Material Info	
Engineering Number	7606.5915.0



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

China RoHS

Missing Compliance
Data

Halogen-Free
Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[93601](#) Series

Mates With
[936010437](#) Female Crimp Contact Insert

Use With
Turned Contacts - Male

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0438](#)