

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010476

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Turned Crimp Contact for 5A D-Sub Inserts and Modules, Female, Gold (Au) Plated Copper Alloy, 0.08-0.20mm² (28-24 AWG), 100 per Bag

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
UPC	887191892849
Physical	
Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Gold
Net Weight	0.210/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	5.00mm
Wire Size AWG	24-28
Wire Size mm²	0.08-0.20
Electrical	
Current - Maximum per Contact	5.0A
Material Info	
Engineering Number	7700.3436.1
Reference - Drawing Numbers	
Sales Drawing	936010476-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Mates With

93601 Male Turned Crimp Contact

Use With

D-Sub Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0476