

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010515](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Crimp Contact Power Module, Female, 2-Pole, 40A, for Crimp Contacts, Grey

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E249674

General

Product Family Industrial Connectors / Enclosures
Series [93601](#)
Component Type Power Module
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
Product Category Heavy Duty Connectors
Product Name GWconnect
UPC 887191827032

Physical

Color - Resin Grey
Durability (mating cycles max) 500
Flammability UL 94V-0
Gender Male
Material - Housing Polycarbonate
Net Weight 11.100/g
Packaging Type Bag
Polarized to Mating Part Yes
Poles 2
Temperature Range - Operating -40° to +125°C

Electrical

Current - Maximum per Contact 40.0A
Voltage - Maximum 1000V

Material Info

Engineering Number 7702.3242.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Mates With

[936010514](#) Female Power Module

Use With

40.0A Turned Male Crimp Contacts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0515](#)