

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010530

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Crimp Contact Insert, Male, 4-Pole, 40A, for Crimp Contacts, Size «34.2x14.60»

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	«34.2x14.6»
Component Type	Inserts - Crimp Contact
Insert Series	S-M40/3/4
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191829678
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	12.000/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	4
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	40.0A
Voltage - Maximum	830V
Material Info	
Engineering Number	7704.3270.0



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Mates With

936010529 Female Crimp Contact Insert

Use With

Turned Contacts - Male

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0530