

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010547

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect D-Sub Insert, Female, 9-Pole, 5A, for Turned Crimp Contacts, Size «34.2x14.5»

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	«34.2x14.5»
Component Type	Inserts - D-Sub
Insert Series	S-MD/9
Material - Metal	Zinc Alloy
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	EN 60664-1, EN 61984, UL 1977
UPC	887191832784
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Female
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	30.600/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	9
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	5.0A
Voltage - Maximum	50V
Material Info	
Engineering Number	7709.3466.0



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Mates With

936010548 Male Crimp Contact D-Sub Insert

Use With

Turned Crimp Contacts - Female

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0547