

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936010643

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect STD - Standard, Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, Size 3A «21x21», Pg11 Thread, Black

Documents:

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93601</u>
Comments	IP67 with screw gasket.
Component Size	3A «21x21»
Component Type	Single Lever Coupler
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191839509

Physical

Entry Location	Top
Flammability	UL 94V-0
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Polyamide
Material - Lever	Polyamide
Net Weight	16.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg11
Thread Type	(Pg)

Electrical

Voltage - Maximum	230V / 400V
-------------------	-------------

Material Info

Engineering Number 7803.6211.1

Reference - Drawing Numbers

Sales Drawing	936010643-000
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 3A «21x21» S-A, S-D, and S-Q Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0643