

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010674](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Right Angle, with Gasket, Size 3A«21x21», M20 Thread, Grey White

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series [93601](#)
Comments IP67 with screw gasket.
Component Size 3A «21x21»
Component Type Single Lever Bulkhead Housing
IP Rating IP66, IP67
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
Product Category Heavy Duty Connectors
Product Name GWconnect
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type STD
UPC 887191842011

Physical

Flammability UL 94V-0
Housing Color Grey White RAL 9002
Lock to Mating Part Yes
Material - Gasket NBR
Material - Housing Polyamide
Material - Lever Polyamide
Mounting Style Bulkhead
Net Weight 17.000/g
Number of Levers 1
Packaging Type Bag
Thread Size M20
Thread Type (M) Metric

Electrical

Voltage - Maximum 230V / 400V

Material Info

Engineering Number 7803.6225.0

Reference - Drawing Numbers

Sales Drawing 936010674-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601](#) Series

Use With

Size 3A «21x21» S-A, S-D, and S-Q Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0674](#)