

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010688

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect HE - Harsh Environment, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 3A «21x21», M20 Thread, Black



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Comments		IP67 with screw gasket.
Component Size		3A «21x21»
Component Type		Single Lever Hood
IP Rating		IP66
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type		HE
UPC		887191842752
Physical		
Entry Location		Side
Hood Coating		Polyester Powder
Hood Color		Black RAL 9005
Lock to Mating Part		Yes
Material - Hood		Die-cast Aluminum
Material - Peg		Die-cast Aluminum
Net Weight		20.900/g
Number of Pegs		2
Packaging Type		Bag
Thread Size		M20
Thread Type		(M) Metric
Material Info		
Engineering Number		7803.6230.1

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 3A «21x21» S-A, S-D, and S-Q Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0688