

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010694

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect EMC - Electromagnetic Compatibility, Single Lever Hood, Aluminum, with 1 Lever, Top Entry, Size 3A «21x21», for S-A, S-D, and S-Q Inserts, M20 Thread

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	IP67 with screw gasket., IP67 with screw gasket.
Component Size	3A «21x21»
Component Type	Single Lever Hood
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191843414
Physical	
Entry Location	Top
Lock to Mating Part	Yes
Material - Hood	Aluminum
Material - Lever	Stainless Steel
Net Weight	29.160/g
Number of Levers	1
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7803.6232.4



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 3A «21x21» S-A, S-D, and S-Q Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0694](#)