

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936010779
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect HP-HE - High Performance-Harsh Environment, Surface Mount Housing, Toggle Locking, Zinc Alloy, Side Entry, Size 6B «44x27», Pg16x2 Thread, Black

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Toggle Locking
Component Size	6B «44x27»
Component Type	Surface Mount Housing
IP Rating	IP68, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191849065
Physical	
Housing Coating	Epoxy-Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Zinc Alloy
Mounting Style	Surface Mount
Packaging Type	Bag
Thread Size	Pg16x2
Thread Type	(Pg)
Material Info	
Engineering Number	7806.3957.3



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free
Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

Use With
Size 6B «44x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0779