

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010821

Status:

Active

Overview:

GWconnect® Heavy Duty Connectors (HDC)

Description:

GWconnect EMC - Electromagnetic Compatibility, Single Lever Surface Mount Housing, Aluminum, with 1 Lever, with Gasket, Size 6B «44x27», Pg16x2 Thread, Low Construction



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	6B «44x27»
Component Type	Single Lever SMT Housing
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191851785
Physical	
Material - Gasket	NBR
Material - Housing	Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Net Weight	185.500/g
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg16x2
Thread Type	(Pg)
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7806.6302.4

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 6B «44x27» S-DD, S-E, S-ES, S-EP, S-EE, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0821](#)