

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936010870
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect EMC - Electromagnetic Compatibility, Single Lever Hood, Aluminum, with 2 Pegs, Top Entry, Size 6B «44x27», without Gasket, M32 Thread, High Construction

Documents:
RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	6B «44x27»
Component Type	Single Lever Hood
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191855271
Physical	
Entry Location	Top
Lock to Mating Part	Yes
Material - Hood	Aluminum
Material - Peg	Stainless Steel
Net Weight	164.300/g
Number of Pegs	2
Packaging Type	Bag
Thread Size	M32
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7806.6450.9



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free
Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Use With
Size 6B «44x27» S-DD, S-E, S-ES, S-EP, S-EE, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0870