

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010900

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect EMC - Electromagnetic Compatibility, Single Lever Hood, Aluminum, with 2 Pegs, Side Entry, Size 6B «44x27», without Gasket, with Pg16 Extended Thread, High Construction



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	6B «44x27»
Component Type	Single Lever Hood
IP Rating	IP66, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191857374
Physical	
Entry Location	Side
Lock to Mating Part	Yes
Material - Hood	Aluminum
Material - Peg	Stainless Steel
Net Weight	97.500/g
Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7806.6502.4

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 6B «44x27» S-DD, S-E, S-ES, S-EP, S-EE, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0900