

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010904](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Top Entry, Size 6B «44x27», Extended Pg16 Thread, Grey

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series [93601](#)
Component Size 6B «44x27»
Component Type Single Lever Hood
IP Rating IP66
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
Product Category Heavy Duty Connectors
Product Name GWconnect
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type STD
UPC 887191858012

Physical

Entry Location Top
Hood Coating Polyester Powder
Hood Color GREY RAL 7037
Lock to Mating Part Yes
Material - Hood Die-cast Aluminum
Material - Peg Stainless Steel
Net Weight 91.000/g
Number of Pegs 2
Packaging Type Bag
Thread Size Pg16
Thread Type (Pg)

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7806.6504.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601](#) Series

Use With

Size 6B «44x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0904](#)