

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0936010954](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Single Lever Surface Mount Housing, Die-cast Aluminum, with 1 Lever, with Gasket, Size 6B «44X27», M40x2 Thread, High Construction, Grey

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
Series [93601](#)  
Component Size 6B «44x27»  
Component Type Single Lever SMT Housing  
IP Rating IP66  
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
Product Category Heavy Duty Connectors  
Product Name GWconnect  
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
Type STD  
UPC 887191861616

**Physical**

Housing Coating Polyester Powder  
Housing Color Grey RAL 7037  
Lock to Mating Part Yes  
Material - Gasket NBR  
Material - Housing Die-cast Aluminum  
Material - Lever Galvanized Steel  
Mounting Style Surface Mount  
Number of Levers 1  
Packaging Type Bag  
Thread Size M40x2  
Thread Type (M) Metric

**Electrical**

Voltage - Maximum 500V

**Material Info**

Engineering Number 7806.7154.0

**Reference - Drawing Numbers**

Sales Drawing 936010944-000



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

**China RoHS**

China ROHS Green Image  
ELV Not Relevant  
RoHS Phthalates Not Contained

**Search Parts in this Series**

[93601](#) Series

**Use With**

Size 6B «44x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0954](#)