

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010998](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Single Lever Surface Mount Housing, Die-cast Aluminum, with 1 Lever, with Cover, with Gasket, Size 6B «44x27», M40 Thread, High Construction, Grey

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series [93601](#)
Color - Cable Jacket N/A
Component Size 6B «44x27»
Component Type Single Lever SMT Housing
IP Rating IP66
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
Product Category Heavy Duty Connectors
Product Name GWconnect
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type STD
UPC 887191864457

Physical

Cover Coating Polyester Powder
Cover Color Grey RAL 7037
Housing Coating Polyester Powder
Housing Color Grey RAL 7037
Lock to Mating Part Yes
Material - Cover Die-cast Aluminum
Material - Gasket NBR
Material - Housing Die-cast Aluminum
Material - Lever Galvanized Steel
Mounting Style Surface Mount
Net Weight 358.000/g
Number of Levers 1
Packaging Type Bag
Thread Size M40
Thread Type (M) Metric

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7806.7267.0

Reference - Drawing Numbers

Sales Drawing 936010993-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Use With

Size 6B «44x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0998](#)