

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936011010

Status: Active

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 1 Lever, Right Side Entry, Size 6B «44x27», Extended Pg16 Thread, Grey



Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	6B «44x27»
Component Type	Single Lever Hood
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Type	STD
UPC	887191865171
Physical	
Entry Location	Side
Material - Hood	Die-cast Aluminum
Material - Lever	Galvanized Steel
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7806.7453.0

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

93601 Series

Use With

Size 6B <<44x27>> S-DD, S-E, S-EE, S-EP,
S-ES, and S-M Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1010](#)