

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011023](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size «32x13», M20 Thread, Grey

Documents:

3D Model	3D Model (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	«32X13»
Component Type	Single Lever Hood
IP Rating	IP66, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191865904

Physical

Cable Diameter	6.00-14.00mm
Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Die-cast Aluminum
Net Weight	172.000/g
Number of Pegs	2
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric

Material Info

Engineering Number	7808.6650.5
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	936011023-000
---------------	---------------



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[93601](#) Series

Use With

Size «32x13» S-QD Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1023](#)