

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011032](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Top Entry, Size «32x13», M25 Thread, Grey

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series [93601](#)
Component Size «32X13»
Component Type Single Lever Hood
IP Rating IP66, IP69
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
Product Category Heavy Duty Connectors
Product Name GWconnect
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type STD
UPC 887191866598

Physical

Cable Diameter 11.00-18.00mm
Entry Location Top
Hood Coating Polyester Powder
Hood Color GREY RAL 7037
Lock to Mating Part Yes
Material - Hood Die-cast Aluminum
Material - Peg Die-cast Aluminum
Number of Pegs 2
Packaging Type Bag
Thread Size M25
Thread Type (M) Metric

Material Info

Engineering Number 7808.6655.5

Reference - Drawing Numbers

Sales Drawing 936011029-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[93601](#) Series

Use With

Size «32x13» S-QD Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-1032