This document was generated on 03/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936011063

Status: Active

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect HP-HE - High Performance-Harsh Environment, Screw Locking Hood, Zinc Alloy, Top Entry, Size 10B «57x27», Pg16 Thread, Black

Documents:
RoHS Certificate of Compliance (PDF)

Series image - Reference only

EU ELV
Not Relevant

EU RoHS	**China RoHS**
Not Reviewed	

REACH SVHC
Not Reviewed
Halogen-Free Status
Not Reviewed
For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Screw Locking Hood
IP Rating	IP68, IP69
Number of Screws	2
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191868707

Physical

Entry Location	Top
Hood Coating	Epoxy-Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Zinc Alloy
Net Weight	475.000/g
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Material Info

Engineering Number	7810.3630.8

Search Parts in this Series
93601 Series

Use With
Size 10B «57x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-EEE, S-HSB, S-K and S-M Inserts

This document was generated on 03/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:
93601-1063