

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936011106
Status: Active
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect HP-HE - High Performance-Harsh Environment, Surface Mount Housing, Toggle Locking, Zinc Alloy, Side Entry, Size 10B «57x27», M20 Thread, Black

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Toggle Locking
Component Size	10B «57X27»
Component Type	Surface Mount Housing
IP Rating	IP68, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191871639
Physical	
Housing Coating	Epoxy-Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Zinc Alloy
Mounting Style	Surface Mount
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric
Material Info	
Engineering Number	7810.3963.3



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Use With
Size 10B «57x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1106](#)