

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936011343

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 2 Levers, Side Entry, Size 10B «57x27», M32 Extended Threaded Fitting, High Construction, Grey



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Double Lever Hood
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191885506
Physical	
Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Lever	Galvanized Steel
Net Weight	310.000/g
Number of Levers	2
Packaging Type	Bag
Thread Size	M32
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7810.5100.0

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status

Not Reviewed

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93601 Series

Use With

Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1343](#)