

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936011744
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect HE-HV - Harsh Environment-High Voltage, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 10B «57x27», M20 Extended Thread, Black

Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Double Lever Hood
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HE-HV
UPC	887191845692
Physical	
Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	122.500/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	830V
Material Info	
Engineering Number	7810.6569.3



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status	
Not Reviewed	
Need more information on product environmental compliance?	
Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Use With
Size 10B «57x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-1744