

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011995](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect EMC - Electromagnetic Compatibility, Double Lever Surface Mount Housing, Aluminum, with 2 Levers, with Gasket, Size 10B «57x27», M40 Thread, High Construction



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Double Lever SMT Housing
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191863207
Physical	
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Housing	Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Number of Levers	2
Packaging Type	Bag
Thread Size	M40
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7810.7462.4

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

Use With
Size 10B «57x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-HSB, S-K and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-1995