

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936012073

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect HP-HE - High Performance-Harsh Environment, Screw Locking Hood, Zinc Alloy, Size 16B «77x27», M50 Thread, Black

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16B «77X27»
Component Type	Screw Locking Hood
IP Rating	IP68, IP69
Number of Screws	2
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191868783
Physical	
Entry Location	Side
Hood Coating	Epoxy-Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Zinc Alloy
Net Weight	545.000/g
Packaging Type	Bag
Thread Size	M50
Thread Type	(M) Metric
Material Info	
Engineering Number	7816.3666.8



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 16B «77x27» S-D, S-DD, S-E, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2073](#)