

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012161

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect HE - Harsh Environment, Single Lever Bulkhead Mount Housing, Die-cast Aluminum, with 1 Lever, with Cover, Size 16A «66x16», Black

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93601</u>
Component Size	16A «66X16»
Component Type	Single Lever Bulkhead Housing
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HE
UPC	887191874166

Physical

Cover Coating	Polyester Powder
Cover Color	Black RAL 9005
Housing Coating	Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Die-cast Aluminum
Material - Lever	Stainless Steel
Mounting Style	Bulkhead
Net Weight	128.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	N/A
Thread Type	N/A

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7816.4544.1



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 16A «66x16» S-A and S-D Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2161](#)