

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012285

Status: Active

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect STD - Standard, Double Lever Bulkhead Mount Housing, Die-cast Aluminum, with 4 Pegs, With Cover, with Gasket, Size 16B «77x27», Grey

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series 93601
Component Size 16B «77X27»
Component Type Double Lever Bulkhead Housing
IP Rating IP66
Overview GWconnect Heavy Duty Connectors (HDC)
Product Category Heavy Duty Connectors
Product Name GWconnect
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984

Type STD
UPC 887191881409

Physical

Cover Coating Polyester Powder
Cover Color Grey RAL 7037
Housing Coating Polyester Powder
Housing Color Grey RAL 7037
Lock to Mating Part Yes
Material - Cover Die-cast Aluminum
Material - Gasket NBR
Material - Housing Die-cast Aluminum
Material - Peg Stainless Steel
Mounting Style Bulkhead
Net Weight 136.900/g
Number of Pegs 4
Packaging Type Bag
Thread Size N/A
Thread Type N/A

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7816.5055.0

Reference - Drawing Numbers

Sales Drawing 936012285-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

93601 Series

Use With

Size 16B «77X27» S-D, S-DD, S-E, S-EE,
S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M,
and S-EHV Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-2285