

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0936012339  
**Status:** Active  
**Overview:** GWconnect® Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD-HV - Standard-High Voltage, Double Lever Hood, Die-cast Aluminum, with 2 Levers, Side Entry, Size 16B «77x27», M32 Thread, Grey



**Documents:**  
RoHS Certificate of Compliance (PDF)

|                             |                                                         |
|-----------------------------|---------------------------------------------------------|
| <b>Agency Certification</b> |                                                         |
| CSA                         | 256883                                                  |
| UL                          | E249674                                                 |
| <b>General</b>              |                                                         |
| Product Family              | Industrial Connectors / Enclosures                      |
| Series                      | 93601                                                   |
| Component Size              | 16B «77X27»                                             |
| Component Type              | Double Lever Hood                                       |
| IP Rating                   | IP66, IP69                                              |
| Overview                    | GWconnect® Heavy Duty Connectors (HDC)                  |
| Product Category            | Heavy Duty Connectors                                   |
| Product Name                | GWconnect                                               |
| Standard                    | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                        | STD-HV                                                  |
| UPC                         | 887191884943                                            |
| <b>Physical</b>             |                                                         |
| Entry Location              | Side                                                    |
| Hood Coating                | Polyester Powder                                        |
| Hood Color                  | GREY RAL 7037                                           |
| Lock to Mating Part         | Yes                                                     |
| Material - Hood             | Die-cast Aluminum                                       |
| Material - Lever            | Galvanized Steel                                        |
| Number of Levers            | 2                                                       |
| Packaging Type              | Bag                                                     |
| Thread Size                 | M32                                                     |
| Thread Type                 | (M) Metric                                              |
| <b>Electrical</b>           |                                                         |
| Voltage - Maximum           | 830V                                                    |
| <b>Material Info</b>        |                                                         |
| Engineering Number          | 7816.5094.2                                             |

**EU ELV**

Not Reviewed

**EU RoHS**

Not Reviewed

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

Not Reviewed

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

93601 Series

**Use With**

Size 16B «77x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2339](#)