

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936012638

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 1 Lever, Top Entry, Size 16B «77x27», Pg29 Extended Threaded Fitting, Grey, High Construction

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Component Size		16B «77X27»
Component Type		Single Lever Hood
IP Rating		IP66
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type		STD
UPC		887191838748
Physical		
Entry Location		Top
Hood Coating		Polyester Powder
Hood Color		GREY RAL 7037
Lock to Mating Part		Yes
Material - Hood		Die-cast Aluminum
Material - Lever		Galvanized Steel
Net Weight		341.200/g
Number of Levers		1
Packaging Type		Bag
Thread Size		Pg29
Thread Type		(Pg)
Electrical		
Voltage - Maximum		500V
Material Info		
Engineering Number		7816.6440.0



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 16B «77x27» S-D, S-DD, S-E, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2638](#)