

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012729
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect HE - Harsh Environment, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 16B «77x27», Pg21 Thread, Black

Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16B «77X27»
Component Type	Single Lever Hood
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HE
UPC	887191845029
Physical	
Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	227.000/g
Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7816.6481.6



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Use With
Size 16B «77x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-K, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2729](#)