

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012803
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect STD-HV - Standard-High Voltage, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Top Entry, Size 16B «57x27», Extended M32 Thread, Grey

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series 93601
Component Size 16B «77X27»
Component Type Single Lever Hood
IP Rating IP66, IP69
Overview GWconnect® Heavy Duty Connectors (HDC)
Product Category Heavy Duty Connectors
Product Name GWconnect
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type STD-HV
UPC 887191850009

Physical

Entry Location Top
Hood Coating Polyester Powder
Hood Color GREY RAL 7037
Lock to Mating Part Yes
Material - Hood Die-cast Aluminum
Material - Peg Stainless Steel
Net Weight 142.000/g
Number of Pegs 2
Packaging Type Bag
Thread Size M32
Thread Type (M) Metric

Electrical

Voltage - Maximum 830V

Material Info

Engineering Number 7816.6547.2



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 16B «77x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2803](#)