

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012823

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect EMC - Electromagnetic Compatibility, Double Lever Hood, Aluminum, with 4 Pegs, Side Entry, Size 16B «77x27», without Gasket, M25 Extended Thread

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93601</u>
Component Size	16B «77X27»
Component Type	Double Lever Hood
IP Rating	IP66, IP69
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191851402

Physical

Entry Location	Side
Lock to Mating Part	Yes
Material - Hood	Aluminum
Material - Peg	Stainless Steel
Net Weight	160.600/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7816.6571.4



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 16B «57x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-HSB, S-K and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2823](#)