

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012885
Status: Active
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect HE - Harsh Environment, Cover, Die-cast Aluminum, with 4 Pegs, without Gasket, Size 16B «77x27», Black



Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	With nylon wire tether line.
Component Size	16B «77X27»
Component Type	Cover
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HE
UPC	887191855844
Physical	
Cover Coating	Polyester Powder
Cover Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	52.900/g
Number of Pegs	4
Packaging Type	Bag
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7816.6806.1

EU ELV Not Relevant	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Use With
Size 16B «77x27» HE Inserts and Hoods/
Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2885](#)