

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012939

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect STD - Standard, Single Lever Surface Mount Housing, Die-cast Aluminum, with 1 Lever, with Gasket, Size 16B «77x27», M40 Thread, High Construction, Grey

Documents:

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93601</u>
Color - Cable Jacket	N/A
Component Size	16B «77X27»
Component Type	Single Lever SMT Housing
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191859712

Physical

Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Net Weight	384.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	M40
Thread Type	(M) Metric

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7816.7171.0

Reference - Drawing Numbers

Sales Drawing	936012933-000
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 16B «77x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-2939