


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936013056

Status: Active

Overview: GWconnect® Heavy Duty Connectors (HDC)

Description: GWconnect STD-HV - Standard-High Voltage, Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 16B <<77x27>>, Pg29 Thread, High Construction, Grey



Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16B <<77X27>>
Component Type	Double Lever SMT Housing
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD-HV
UPC	887191867762
Physical	
Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Net Weight	378.000/g
Number of Levers	2
Packaging Type	Bag
Thread Size	Pg29
Thread Type	(Pg)
Electrical	
Voltage - Maximum	830V
Material Info	
Engineering Number	7816.7475.2

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 16B <<77x27>> , S-EHV Inserts with Screw Terminals and S-HSB Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3056](#)