

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936013234

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Double Lever Bulkhead Mount Housing, Die-cast Aluminum, with 4 Pegs, With Cover, with Gasket, Size 24B «104x27», Grey



Series image - Reference only

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	24B «104X27»
Component Type	Double Lever Bulkhead Housing
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191878737
Physical	
Cover Coating	Polyester Powder
Cover Color	Grey RAL 7037
Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Peg	Stainless Steel
Mounting Style	Bulkhead
Net Weight	163.000/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	N/A
Thread Type	N/A
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7824.5056.0
Reference - Drawing Numbers	
Sales Drawing	936013234-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 24B «104X27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3234](#)