

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936013478](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect STD-HV - Standard-High Voltage, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 24B «104x27», Grey, with IP66 -Ribbon Cable Gland, Grey, Cable Size 3.80-9.00mm x 48.00-56.00mm, High Construction

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Cable Gland Type	IP66 - Ribbon Cable
Component Size	24B «104X27»
Component Type	Double Lever Hood
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD-HV
UPC	887191893525
Physical	
Entry Location	Top
Flammability	UL 94V-0
Gland Color	Grey RAL 7037
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Gasket	Silicone
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	432.000/g
Number of Pegs	4
Packaging Type	Bag
Ribbon Cable Size	3.80-9.00mm X 48.00-56.00mm
Temperature Range - Operating	-40° to +100°C
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP66, IP69
Electrical	
Voltage - Maximum	830V
Material Info	
Engineering Number	7824.5373.2



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

Use With
Size 24B «104x27» , S-EHV Inserts with Screw Terminals, S-HSB Inserts, and Ribbon Cable

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3478](#)