

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936013484

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 24B «104x27», Grey, with IP66 - Ribbon Cable Gland, Grey, Cable Size 4.50-5.70mm x 72.00-76.00mm, High Construction

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Cable Gland Type		IP66 - Ribbon Cable
Component Size		24B «104X27»
Component Type		Double Lever Hood
IP Rating		IP66
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type		STD
UPC		887191893846
Physical		
Entry Location		Top
Flammability		UL 94V-0
Gland Color		Grey RAL 7037
Hood Coating		Polyester Powder
Hood Color		GREY RAL 7037
Lock to Mating Part		Yes
Material - Cable Gland		Polyamide
Material - Gasket		Silicone
Material - Hood		Die-cast Aluminum
Material - Peg		Stainless Steel
Net Weight		425.000/g
Number of Pegs		4
Packaging Type		Bag
Ribbon Cable Size		4.50-5.70mm X 72.00-76.00mm
Temperature Range - Operating		-40° to +100°C
Thread Size		N/A
Thread Type		N/A
Waterproof / Dustproof		Yes
Waterproof / Dustproof Type		IP66, IP69
Electrical		
Voltage - Maximum		500V
Material Info		
Engineering Number		7824.5375.0



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K,S-M, and S-EHV Inserts and Ribbon Cable

This document was generated on 03/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3484](#)