

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936014104

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Double Lever Surface Mount Housing, Die-cast Aluminum, with 4 Pegs, with Cover, with Gasket, Size 32A «66x40», Pg21 Thread, Grey



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Component Size		32A «66x40»
Component Type		Double Lever SMT Housing
IP Rating		IP66
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type		STD
UPC		887191881553
Physical		
Cover Coating		Polyester Powder
Cover Color		Grey RAL 7037
Housing Coating		Polyester Powder
Housing Color		Grey RAL 7037
Lock to Mating Part		Yes
Material - Cover		Die-cast Aluminum
Material - Gasket		NBR
Material - Housing		Die-cast Aluminum
Material - Peg		Stainless Steel
Mounting Style		Surface Mount
Number of Pegs		4
Packaging Type		Bag
Thread Size		Pg21
Thread Type		(Pg)
Electrical		
Voltage - Maximum		500V
Material Info		
Engineering Number		7832.4616.0

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 32A «66x40» S-A and S-D Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4104