

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0936014170](#)  
**Status:** **Active**  
**Overview:** [GWconnect® Heavy Duty Connectors \(HDC\)](#)  
**Description:** GWconnect HE - Harsh Environment, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 32A «66x40», Pg29 Extended Threaded Fitting, High Construction, Black



**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

|                             |                                                         |
|-----------------------------|---------------------------------------------------------|
| <b>Agency Certification</b> |                                                         |
| CSA                         | 256883                                                  |
| UL                          | E249674                                                 |
| <b>General</b>              |                                                         |
| Product Family              | Industrial Connectors / Enclosures                      |
| Series                      | <a href="#">93601</a>                                   |
| Component Size              | 32A «66x40»                                             |
| Component Type              | Double Lever Hood                                       |
| IP Rating                   | IP66, IP69                                              |
| Overview                    | <a href="#">GWconnect® Heavy Duty Connectors (HDC)</a>  |
| Product Category            | Heavy Duty Connectors                                   |
| Product Name                | GWconnect                                               |
| Standard                    | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                        | HE                                                      |
| UPC                         | 887191885360                                            |
| <b>Physical</b>             |                                                         |
| Entry Location              | Side                                                    |
| Hood Coating                | Polyester Powder                                        |
| Hood Color                  | Black RAL 9005                                          |
| Lock to Mating Part         | Yes                                                     |
| Material - Hood             | Die-cast Aluminum                                       |
| Material - Peg              | Stainless Steel                                         |
| Number of Pegs              | 4                                                       |
| Packaging Type              | Bag                                                     |
| Thread Size                 | Pg29                                                    |
| Thread Type                 | (Pg)                                                    |
| <b>Electrical</b>           |                                                         |
| Voltage - Maximum           | 500V                                                    |
| <b>Material Info</b>        |                                                         |
| Engineering Number          | 7832.4654.1                                             |

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[93601](#) Series

**Use With**

Size 32A 66x40» S-A and S-D Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4170](#)